


HOW THE IRT/C TEMPERATURE SELECTION GUIDE WORKS

All IRt/c's are self-powered devices, which rely on the incoming infrared radiation to produce the signal through thermoelectric effects. Accordingly, the signal will follow the rules of radiation thermal physics, and be subject to the non-linearities inherent in the process.




The linear region matches the conventional t/c to a specified tolerance.


However, over a range of temperatures, the IRt/c output is sufficiently linear to produce a signal which can be interchanged directly for a conventional t/c signal. For example, specifying a 2% match to t/c linearity results in a temperature range in which the IRt/c will produce a signal within 2% of the conventional t/c operating over that range. Specifying 5% will produce a somewhat wider range, etc.

Each IRt/c model is specifically designed for optimum performance in the region of best linear fit with conventional t/c's, but can be used outside

of this range by simply calibrating the readout device appropriately. The output signal is smooth and continuous over its entire rated temperature range, and maintains 0.01°C repeatability over its entire range.




The actual signal generated by the IRt/c can be approximated with a fourth order polynomial function of target temperature. This fourth power dependence is due to radiation physics, and not a limitation of the IRt/c.



Signal produced by the IRt/c-K-80F/27C has its 2% linear range centered at 80°F (27°C), but produces a repeatable signal to 1200°F (650°C).

The Temperature Selection Guide is a summary of the linear range performance of each IRt/c model.



Exergen Global offices:

The Netherlands
 Pastoor Clercxstraat 26
 5465 RH Veghel
 Tel: +31(0) 413 37 65 99
 Fax: +31(0) 413 37 93 10

USA
 400 Pleasant Street
 Watertown, MA 02472
 Tel: +1 617 649 6322
 Fax: +1 617 923 9911

office@exergenglobal.com
 www.exergenglobal.com