



# FIFO Bleeding Wheel


 SKAGINN 3X

- First-in, first-out principle - FIFO
- Ensures optimal and equal bleeding for each fish
- Adjustable controls for all bleeding parameters
- Compact design - buffering and bleeding in a single unit



Bleeding is a critical step in fish processing. Optimal bleeding ensures the elimination of blood color in white fish and blackening in value-added (e.g. smoked) oily fish such as salmon or trout. Furthermore, efficient bleeding has been proven to reduce bacterial count and increase total product quality.

The FIFO Bleeding Wheel can be fitted into any type of workflow on land or at sea, wild or farmed as well as white or oily fish processing.



## First-in, First-out - FIFO

The Skaginn 3X FIFO Bleeding Wheel uses the first-in, first-out process, which ensures that the first fish that enter the bleeding wheel will also be the first to leave. This enables secure traceability.

The design of the bleeding wheel keeps fish together in unique groups, which then travel as a batch through the rest of the system. This batching supports full traceability as each batch is automatically recorded and tracked by computer.

## Gentle Handling


The gentle back-and-forth tumbling action of the drum combined with a mechanically generated current replicate the natural movement of the fish through water, expelling the blood from of the tissue.

## Full Control of Bleeding Parameters

The FIFO Bleeding Wheel comes equipped with a digital interface that gives you total control of the bleeding process.

The programmable control parameters include:

- Bleeding time - programable user parameters
- Tumbling intensity (optional)
- Water supply timing
- Water supply amount
- Configure batches (according to size, type, batch total weight)



## Compact Design - Buffer and Bleed in a Single Unit

Despite the unit's size, its maximum batch size can range anywhere from 100 kg to 600 kg. The pre-buffer stores up to 100 kg of fish before bleeding and maintains an effective flow through process.