

BONDLINE 2490

SILVER FILLED ADHESIVE

Bondline 2490 is a silver filled, electrically conductive epoxy. This premixed, frozen and solvent free epoxy adhesive is designed for microelectronic chip bonding, with high Tg and high shear strength.

ADHESIVE PROPERTIES

Color	Silver
Viscosity*	27,000 cps
Work Life @ 25°C	7 days
Hardness (Shore D)	90
Cure Options	5 minutes @ 150°C or 20 minutes @ 120°C or
Service Temperature Range	-55°C to 175°C
Lap Shear Strength @ 25°C (Al to Al)	3000 psi
@ 150°C (Al to Al):	2100 psi
Volume Resistivity**	.00003 ohm cm.
Specific Gravity	3.06
Glass Transition Temperature (Tg)***	143°C
Weight Loss (TGA) @ 85°C	Nil
@ 105°C	Nil
Coefficient of Thermal Expansion***	
Above Tg	37x 10 ⁻⁶ in/in/°C
Below Tg	204 x 10 ⁻⁶ in/in/°C
Shelf Life	7 days @ 25°C 6 months @ 5°C 1 year @ -40°C
Availability	Net volume 1cc to 2.5cc, available in disposable 3cc syringes.

Adhesive properties are not intended to be used as specification limits.

* Brookfield Viscometer DV-II+, Spindle CP51, 10 rpm speed @ 25°C

** When a mass larger than a small dot needs to be cured, it must be B-Staged @ 75°C for 1 hour before curing @ 120°C or higher temperature.

*** Cured 20 minutes @ 120°C

GENERAL INSTRUCTIONS FOR ADHESIVE STORAGE/ USE

FROZEN STORAGE

This adhesive must be stored at (minus) -40°C (°F) or colder at all times. Storing this adhesive at temperatures warmer than (minus) -40°C (°F) will shorten its work life.

DO NOT RE-FREEZE adhesive that has already been thawed!

THAWING PROCESS

Remove frozen syringe from freezer. Place in vertical position with lure lock end pointed down during thaw.

Adhesive must reach room temperature before use. See chart below based on syringe size.

SYRINGE SIZE	THAW TIME
1cc	5 minutes
3cc	10 minutes
5cc	15 minutes
10cc	20 minutes

SURFACE PREPARATION

Make sure that all surface areas to be bonded are free of any contamination. If parts have been solvent cleaned make sure solvent is dried before applying adhesive

APPLICATION

Check the work life of the adhesive, on the technical data sheet. Adhesives must be used within its work life .The adhesives' properties will change if it is used past the allowable work life. Apply adhesive using dispensing equipment of choice. Contact Bondline Technical Service with questions about dispensing adhesives.

CURE

Choose a Cure Option (time & temperature) from the Bondline technical data sheet. Preheat the oven to the temperature of the selected cure option. For optimum cure, do not deviate from the selected cure option. Be sure to allow additional time for holding fixtures to reach cure temperature. Avoid opening oven doors during cure. Large fixtures and/or multiple fixtures may require extended cure time.

SAFETY

Review the adhesive Safety Data Sheet (SDS) before using. Refer to the SDS in case of emergency. Always wear protective gloves and goggles while handling adhesives. Only work with adhesives in well-ventilated areas, with curing ovens vented outside. For industrial use only.

TECHNICAL SERVICE CONTACT

For recommendations and help with any aspect of adhesive applications please contact the Bondline Technical Service Department (408) 830-9200, or via email: info@bondline.net or visit our website, www.bondline.net

CAUTION: For industrial use only. People with sensitive skin may have a reaction to this adhesive. Avoid skin contact. Wash all areas with soap and water immediately if contact does occur. It is important to refer to Safety Data Sheet (SDS) OSHA for more details.

© Bondline Electronic Adhesives, Inc. All rights reserved. All trademarks and registered trademarks belong to their respective owners. Notice to User: The information contained herein is based on technical data and tests which we believe reliable. It should be used by persons who have technical skill, at their own discretion and risk. Since conditions of use are outside of Bondline's control, we can assume no liability of results obtained or damages incurred through the application of data presented. Bondline's sole liability is limited to refund of purchase price of any product shown to be defective.